


# Multi-Tek® Analyzer — Total Sulfur Analysis in Liquids and Solids



- ◆ Total sulfur, total nitrogen analysis
- ◆ ASTM D5453 Standard Test Method
- ◆ Fast analysis process
- ◆ Sulfur level detection limit: 0.3 ppm (RSD: 0.5-5%)

## Sulfur Testing and Analysis Services

Professionally trained scientists provide sulfur analysis services for customers in industries, startups, research, and academic organizations:

- Fuel and Oil, Biodiesel, Biofuels
- Farming Products, Chemicals, Residues, Soil
- General Chemical and Specialty Chemical
- Cosmetic and Ethyl Alcohol Products

Compare the analysis limitation with other industrial service labs:

Service provider	Technique	Sulfur detection limit	Sample size per single
Microana, inc.	ICP-MS, UVF	10 ppm	10 ml
SWRI	XRF	10 ppm	80 ml
<b>AdEM</b>	<b>Multi-Tek® UVF</b>	<b>0.3 ppm</b>	<b>1 ml</b>

\*Price per sample/batch upon request



## **Advanced Energy Materials, LLC.**

***advancedenergymat.com***

311 East Lee St.  
Louisville, KY 40208  
Phone: 502-499-0095  
E-mail: [Juan.He@advancedenergymat.com](mailto:Juan.He@advancedenergymat.com)